

V 블록, 수직형


품목 설명/제품 이미지



설명


재질:
단강.

표면 마무리:
검정 산화 처리
V 블록면과 접촉면 연마됨



V 블록, 수직형

도면



품목 요약

V 블록, 수직형

주문 번호	A	B Ø 통과 볼트용	C min.	C max.	C 테스트-Ø	D	E	F	부속 통과 볼트
K0819.60512063	63	12 F7	15	80	50±0,003	32	95,071	$C/2 \times \sqrt{2} + 34,716$	K0815.112065
K0819.60512075	75	12 F7	15	100	70±0,003	32	124,142	$C/2 \times \sqrt{2} + 39,645$	K0815.112065
K0819.60516063	63	16 F7	15	80	50±0,003	25	95,071	$C/2 \times \sqrt{2} + 34,716$	K0815.116065
K0819.60516075	75	16 F7	15	100	70±0,003	25	124,142	$C/2 \times \sqrt{2} + 39,645$	K0815.116065